

ITEM	QTY	MATERIAL	CUT 1	CUT 2	PART	NAME	#/EACH
1	2	RECTANGULAR TUBE, CS, 8x4x3/16	139.00		A-25324-A		162.0
2	2	RECTANGULAR TUBE, CS, 8x4x3/16	119.00		A-25324-A		137.8
3	2	RECTANGULAR TUBE, CS, 8x4x3/16	24.000		A-25324-A		29.0
4	4	RECTANGULAR TUBE, CS, 8x4x3/16	7.105		A-25324-A		8.6
5	4	RECTANGULAR TUBE, CS, 8x4x3/16	7.000		A-25324-A		8.5
6	1	CHANNEL, CS, 4x4.5#/FT	35.5		A-05034		13.4
7	1	CHANNEL, CS, 4x4.5#/FT	24.000		A-05034		9.0
8	2	CHANNEL, CS, 3x3.5#/FT	39.500		A-05029		11.6
9	1	ANGLE, CS, 4x4x1/4	7.000		A-xxxxx		3.8
10	1	ANGLE, CS, 4x4x1/4	7.000		A-xxxxx		3.8
11	1	ANGLE, CS, 2x2x1/4	35		A-02085		9.3
12	1	ANGLE, CS, 2x2x1/4	35		A-02085		9.3
13	1	ANGLE, CS, 2x2x1/4	24.000		A-02085		6.4
14	1	ANGLE, CS, 2x2x1/4	24		A-02085		6.4
15	6	ANGLE, CS, 2x2x1/4	7.105		A-02085		1.9
16	1	ANGLE, CS, 2x2x1/4	6.5		A-02085		1.7
17	1	ANGLE, CS, 2x2x1/4	6.5		A-02085		1.7

TOTAL WEIGHT: 825.1 lbm

