

LMS Qsources measurement amplifier

Facilitating fast setup and efficient use of
excitation hardware

LMS/Q-AMP/1/20161215

Benefits

- Place all connectors on the front to allow fast test setup
- Deliver a low self-noise level
- Provide one amplifier for all LMS Qsources hardware

Features

- High-power output
- Fanless housing
- Robust lightweight housing
- Built-in protection that prevents damage to connected excitation equipment

Summary

The LMS™ Qsources hardware measurement amplifier has been designed to power all LMS Qsources structural and acoustic exciters. The Bayonet Neill–Concelman (BNC) input and banana output connectors are chosen to match all LMS Qsources exciters. The amplifier provides a pop-free start-and-stop control. Excessive heat is transferred to its housing, which serves as a heatsink. The absence of a ventilator makes it a low-noise amplifier, essential for acoustic measurements.

It is compatible with all LMS Qsources exciters:

- Low-mid frequency volume source (Q-LMF)
- Mid-high frequency volume source (Q-MHF)
- Miniature volume source (Q-IND)
- High frequency shaker (Q-HSH)
- Miniature shaker (Q-MSH)
- Thumper shaker (Q-TMP)
- Low-frequency monopole source (Q-MED)



LMS Qsources measurement amplifier

Physical specifications

- Dimensions: 200 millimeters (mm) X 260 mm X 72 mm
- Mass: 2.45 kilograms (kg)
- Input connector type: female BNC
- Output connector type: female banana

Performance

- Max input signal voltage: 10 volt (V) peak
- Maximum output voltage: 31 voltage root mean square (Vrms)
- Maximum output current: 6.5 Ampère rms (Arms)
- Amplification (relative to input signal): -32 to 28 decibels (dB)
- Amplification accuracy: 0.5 dB
- Frequency range (+1dB/-3 dB): 10 to 40,000 Hz
- Minimum/maximum output load impedance: 3/100 Ohm nominal
- Self noise level: <20 dB(A)

- Signal to noise ratio: >110 dB
- Available in 115/230V version

Supplied accessories

- User manual
- Power cable
- Flight case

LMS Qsources structural and acoustic exciters

- Low-mid frequency volume source [Q-LMF]
- Mid-high frequency volume source [Q-MHF]
- Miniature volume source [Q-IND]
- High frequency shaker [Q-HSH]
- Miniature shaker [Q-MSH]
- Thumper shaker [Q-TMP]
- Low-frequency monopole source [Q-MED]



Siemens PLM Software
www.siemens.com/plm

Americas +1 314 264 8499
 Europe +44 (0) 1276 413200
 Asia-Pacific +852 2230 3308

© 2017 Siemens Product Lifecycle Management Software Inc. Siemens and the Siemens logo are registered trademarks of Siemens AG. LMS, LMS Imagine.Lab, LMS Imagine.Lab Amesim, LMS Virtual.Lab, LMS Samtech, LMS Samtech Caesam, LMS Samtech Samcef, LMS Test.Lab, LMS Soundbrush, LMS Smart and LMS SCADAS are trademarks or registered trademarks of Siemens Industry Software NV or any of its affiliates. All other trademarks, registered trademarks or service marks belong to their respective holders.
 34814-A6 1/17 H